

STANLEY[®]
Access Technologies

PERFORMANCE IN ACTION™



ICU/CCU Doors You Can Depend On



INTERACTIVE Table of Contents

The STANLEY Difference	03
STANLEY Door Service	04
Selection Guide	06
› Features	
AUTOMATIC AND MANUAL SLIDING	
› ProCare Innovation	07
› Largest Clear Door Opening	11
› Largest Rough Opening	14
› P-Panel/ Surface Applied	16
Manual Swing Doors	19
Manual Hybrid Swing-Fold Doors	22



82
**YEARS OF EXPERIENCE
AND DEDICATION**

THE STANLEY DIFFERENCE

We are reliable to our core because you depend on us.

Even though we already have the largest geographic footprint in North America, we are continuously expanding our team of R&D and innovation engineers, sales representatives and service and install technicians. This paired with being the only manufacturer with 2 US factories means you can trust us to get what you need, how you need it and when you need it.

We never cut corners when it comes to safety and conformance.

Excellence is equated to making it right the first time, because we know every expertly crafted product we make needs to help you do better, safer, more significant work. Our unwavering mission to adhere to the highest standards of material, workmanship and service since we invented the first swinging automatic door over 80 years ago is the reason we continue to be the industry leader.

Experience and dedication to take you from where you are to where you want to go.

Our job is to help you do yours better, and we take pride in what you make possible. So you get consistency that meets your complete satisfaction, our products are only sold by, shipped by, handled by and installed by dedicated STANLEY employees and partners. Their experience with product solutions, codes and standards, and the industry runs deep; with an average of 12 years for our technicians and 13 years for our sales representatives.

We are a Purpose-driven organization. This is what binds us and drives us to do the impossible. **Together, we can Make The World Accessible.**


DOORS ARE NOT YOUR MOST CRITICAL PIECE OF HEALTHCARE EQUIPMENT. BUT WE BUILD THEM AS IF THEY WERE.

As a service customer, you will receive the expertise of the industry's largest and most experienced automatic door service provider in North America. You can be assured your equipment is kept in top operating condition, planned maintenance is completed as required, parts replacement meet manufacturer's specification, and all activity is appropriately documented thereby minimizing your liability exposure.

For more information visit
stanleyaccess.com/service-support



- 83 Central Locations
- 750+ Technicians With an Average of 12 Years Experience
- ✂ 3 Rebuild Centers
- ☎ 2 Centralized Service Call Centers
- 🏭 3 ISO Certified Manufacturing Facilities
- ✈ 2 Regional Distribution Centers



SELECTION GUIDE

Features

ICU DOOR PRODUCT FEATURES	SLIDING							SWINGING		
	Largest Clear door Opening Per Rough Opening		Modernized	Value Engineered			Automatic		Swing	Hybrid Swing/Fold
	Dura-Care 7500TL	Dura-Care 7500TL-FBO	ProCare 8300	Dura-Care 7000TL	Dura-Care 7200	Dura-Care 7300 TL-FBO	ProCare 8300A	Dura-Care 7500A	Dura-Care 7400	Dura-Care 7600
Rough Opening Range	84.5"-108.5"	84.5"-108.5"	84.5"-108.5"	92.5"-104.5"	84.5"-108.5"	84.5"-108.5"	84.5"-108.5"	84.5"-108.5"	76"-100" (Pair)	84.5"-120.5"
Largest Clear Door Walk-Thru Opening	60.6"	55.5"	50.2"	43.4"	47.3"	50.2"	49.3"	60.6"	91.5" (Pair)	99.8"
Trackless Threshold	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
All Panels Break Out		✓	✓	✓		✓	✓	✓	✓	✓
Only Sliding Panel Breaks Out	✓				✓					
2-Panel Design			✓	✓	✓	✓	✓		✓	
3-Panel Design	✓	✓						✓		✓
P-Panel Design	✓				✓					
Synchronized Panels (Telescopic)	✓								✓	
Smoke & Draft Rated (UL 1784) Option	3-Panel	3-Panel	✓	2-Panel	2-Panel	✓	✓		✓	
2010 FGI Airborne Isolation Infection Room (Closer Required) Positive/Negative Pressure for Isolation Rooms			✓			✓	✓		✓	
STC Rated ¹			✓				✓			
New Catchless Handle			✓				✓			
New Positive Latch Hook Shield			✓				✓			
Optional Positive Latching	✓	✓	✓	✓	✓	✓	✓	✓		
Electronic Privacy Glass Option	✓	✓		✓	✓		✓			
Integral Blinds Option	✓	✓	✓	✓	✓		✓	✓	✓	✓
	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage	Visit Webpage


¹ Requires recommended STC rated glass

*Electric Solenoid Lock

DISCLAIMER: These charts are to illustrate standard versions of our most popular products; for customized options and sizes, or additional panel configurations other than those shown please contact an authorized STANLEY representative.

INNOVATION: PROCARE

Trackless 2-Panel Slide Manual Automatic



SOLUTIONS FOR

- › Rough Opening Width Range: ~84" - 108"
- › Clear Door Opening Width Range: ~33" - 50"
- › Patient Privacy
- › Frequent Swing Out and Reset
- › Infection Control

APPLICATIONS

- › ICU/CCUs
- › Pressurized Isolation Rooms
- › Smoke Rated Rooms
- › Emergency Department Treatment Rooms
- › Pre/Post Surgery Rooms
- › Same Day Surgery Rooms
- › Trauma Rooms
- › Hospital Pharmacies
- › Operating Rooms
- › Corridors

CLEAR DOOR OPENING PER ROUGH OPENING

	7'-0 1/2" Rough Opening	8'-0 1/2" Rough Opening	9'-0 1/2" Rough Opening
ProCare 8300	38.2"	44.2"	50.2"
ProCare 8300A Automatic	37.4"	43.4"	49.4"

THE NEW PROCARE 8300

The industry's only human-centric ICU door deliberately designed with respect for patients and caregivers in sensitive healthcare environments.



Protect the Patient



Widest 2-panel clear door opening in the industry, 44.2" for manual and 43.3" for automatic model with an 8' door. (Image: 8' manual door, 40.5" bed).




Eliminate dangerous snagging of IV lines and equipment with our catch-free contoured handle and retractable positive latch hook shield.

Promote Healing



Easy and more controlled swing out and return with our new instant swing out button.


Quiet and flawless operation every time with our swing out guidance system. No panel sag during swing out.



Add touch-less activation for infection control.

Easily switches to manual slide mode, giving nurses control over the door opening after they leave the room so they can better monitor patients. Exclusive Power Assist Technology makes sliding 3x easier.

2 Panels Swing Out



STANDARD FEATURES

- Swing Out Button (STANLEY Exclusive)
- Swing Out Guidance System (STANLEY Exclusive)

OPTIONS

- Positive Latching With Hook Shield (STANLEY Exclusive)
- Integral Blinds
- Self-Closing^M
- Electronic Privacy Glass^A
- Secure Card Access^A
- Full Energy ANSI/BHMA A156.10^A
- Low Energy ANSI/BHMA A156.38^A

MODELS:

ProCare 8300: Base Model, 2-panel manual sliding door with full swing out at full open.

ProCare 8300A Automatic: 2-panel automatic sliding door with full swing out at full open. Jamb mounted touch-less wave activation and overhead safety sensors, meeting ANSI/BHMA A156.10.

RATINGS*:

Smoke & Draft: Leakage rated under ANSI/UL1784 and labeled as a smoke barrier

- › Smoke and Draft Seals
- › Positive Latching (Electric Strike on 8300A)
- › Identifiable Sticker For Rapid Commissioning

Infection Control: Leakage rated, in compliance with 2014 FGI guidelines for pressurized Airborne Isolation Infection Control Rooms

- › Concealed Bottom Sweeps
- › Perimeter Seals
- › Self-Closing^M

STC Rated: Extra seals and special glass to reduce noise transmission

- › Concealed Bottom Sweeps
- › Glass Stops For Recommended STC Rated Glass
- › Identifiable Sticker For Rapid Commissioning

INFORMATION, VALUE ENGINEERED OPTIONS, SPECS AND DRAWINGS

stanleyaccess.com/procare-8300




**

A: Automatic Version Only

M: Manual Version Only

*Restrictions may apply such as overall frame height, sliding/breakaway panel width and glazing.

**The typical ProCare 8300 Manual model complies with the Buy American Act, as specified in Section 52.225-1 and Section 52.225.11 of Federal Acquisition Regulations, August, 2017.



SOLUTIONS FOR

- › Rough Opening Width Range: 84.5" - 108.5"
- › Clear Door Opening Width Range: 39.5" - 60.6"
- › Patient Privacy
- › Low Swing Out Volume
- › Small Patient Rooms/Corridors: Shorter Swinging Panels



APPLICATIONS

- › ICU/CCUs
- › Pressurized Isolation Rooms
- › Smoke Rated Rooms
- › Emergency Department Treatment Rooms
- › Pre/Post Surgery Rooms
- › Same Day Surgery Rooms
- › Trauma Rooms
- › Large Office/Meeting Rooms
- › Bariatric Treatment Rooms


Largest Clear Door Opening Vs Rough Opening

Trackless
3-Panel Telescoping
Manual
Automatic

Manual



Automatic



Dura-Care 7500 TL-FBO

RATINGS:

Smoke & Draft

STANDARD FEATURES

Recessed Handle
Swing Out Lever

OPTIONS

Self-Closing (External Mount)
Positive Latching
Electronic Privacy Glass
Smoke & Draft Seals
3- or 6-Panels

Dura-Care 7500 TL

RATINGS:

Smoke & Draft

STANDARD FEATURES

Recessed Handle
Push-to-Swing Out
Synchronized Equal Panels

OPTIONS

Self-Closing (External Mount)
Positive Latching
Electronic Privacy Glass
Smoke & Draft Seals
3- or 6-Panels

Dura-Care 7500A

RATINGS

Smoke & Draft

STANDARD FEATURES

Recessed Handle
Push-to-Swing Out
Synchronized Equal Panels

OPTIONS

Self-Closing (External Mount)
Positive Latching
Electronic Privacy Glass
Smoke & Draft Seals
3-Panels

[CLICK HERE TO ASK A QUESTION](#)

DETAILED INFORMATION

stanleyaccess.com/duracare-7500series



7500 TL-FBO
 Bone & Joint
 Institute,
 Hartford, CT
 Perkins and
 Will Architects



**7500 TL with
 Privacy Glass (On)**
 St. Michaels,
 Toronto, CA
 NORR Architects



7500 TL with Privacy Glass (Off)
 STANLEY Healthcare Experience Center
 Waltham, MA



P-Panel/Surface Applied


Trackless 2-, 3-, 4- and 6-Panel Manual

SOLUTIONS FOR


- › Rough Opening Width Range: 35.3" x 106.3"
- › Clear Door Opening Width Range: 35.3" - 91.5"
- › Retrofit

APPLICATIONS

- › Renovations
- › Patient Bathrooms
- › ICU/CCUs
- › Pressurized Isolation Rooms
- › Emergency Department Treatment Rooms
- › Pre/Post Surgery Rooms
- › Same Day Surgery Rooms
- › Trauma Rooms
- › Office/Meeting Rooms



2-Panel Single Slide



Dura-Care 7200


RATINGS:

Customized Base Model
Smoke & Draft
Infection Control (+/- Pressure)

DETAILED INFORMATION

stanleyaccess.com/dura-care-7200-manual-door

4-Panel Bi-Part



Dura-Care 7200


RATINGS:

None

DETAILED INFORMATION

stanleyaccess.com/dura-care-7200-manual-door

3-Panel Telescoping



7500 TL 3-Panel


RATINGS:

NONE

DETAILED INFORMATION

stanleyaccess.com/duracare-7500Series

6-Panel Telescoping Bi-Part



7500 TL 6-Panel

RATINGS:



None

DETAILED INFORMATION

stanleyaccess.com/duracare-7500Series

[CLICK HERE TO ASK A QUESTION](#)





Manual Swing

SOLUTIONS FOR


- › Typical Rough Opening Width: 40.0" - 100.0"
- › Clear Door Opening Width: 33.8" - 91.5"
- › Large Cdo Per Small Rough Opening
- › Simple Solution - End User Ease
- › Tightest Sealing For Positive Pressure
- › Small Rooms And Spaces

APPLICATIONS


- › ICU/CCUs
- › Patient Bathrooms
- › Pressurized Isolation Rooms
- › Emergency Department Treatment Rooms
- › Pre/Post Surgery Rooms
- › Same Day Surgery Rooms
- › Trauma Rooms



Uneven Pair



Pair



Single



Dura-Care 7400

RATINGS:

Smoke & Draft
Infection Control (Positive Pressure)

STANDARD FEATURES

Continuous Hinge
Flush Bolt On Inactive Panels
Positive Latch Handle

OPTIONS

Integral Blinds
Self-Closing On Active Panel
Positive Latching
Bottom Sweeps

DETAILED INFORMATION

stanleyaccess.com/manual-icu-ccu-swing

[CLICK HERE TO ASK A QUESTION](#)




Hybrid Swing-Fold

SOLUTIONS FOR



- › Rough Opening Width Range: 85.5" x 120.5"
- › Clear Door Opening Width Range: 63.8" - 99.8"
- › Versatile Space Needs

APPLICATIONS

- › ICU/CCUs
- › Pressurized Isolation Rooms
- › Emergency Department Treatment Rooms
- › Pre/Post Surgery Rooms
- › Same Day Surgery Rooms
- › Trauma Rooms



Bi-fold and Swing Door System



Dura-Care 7600

RATINGS:

None

STANDARD

Pulls

OPTIONS

Integral Blinds on Swing Leaf

Self-Closing On Active Panel

1-Point Locking

DETAILED INFORMATION

stanleyaccess.com/hybrid-swing-fold

[CLICK HERE TO ASK A QUESTION](#)

STANLEY®

Access Technologies

CONTACT

StanleyAccess.com

Mainline: 1-800-7-ACCESS

Service: 1-888-DOOR-444

QUICK LINKS

[Submit Questions](#)

[Contact The Rep Closest To Your Job Site
Service](#)



MAKE THE

WORLD

ACCESSIBLE